


INTRODUCTION

AntiLog is the ideal way to record all of your RS232 data without requiring PCs, laptops or hand held computers. This simple to use, comprehensive data logging solution can log up to two completely independent channels of serial port data at the same time using V7.0 of the system software. It is ready to log as soon as you press the 'On' button. Push and hold the 'Off' button to stop logging. Repeat as many times as you like to append to the store – it's as simple as that!



Hold the 'On' button down until a green LED lights and then release will put the unit in playback menu mode. Playback menu mode allows you to configure your unit using an easy to use terminal menu system. Recorded data can be replayed or upload to a PC, Laptop or other host machine of your choice. Data can even be played back in 'real time' on up to two RS232 output channels simultaneously to simulate real equipment output.

APPLICABILITY



AntiLog V7.0 system software is available for the original AntiLog range of data loggers as well as the new AntiLogPro units. It works on all boxed and OEM variants with extended features available on the OEM variants as you have access to a dedicated pin header with more signal lines.

For example, V7.0 on AntiLogPro OEM hardware provides support for a third auxiliary serial port. This port can be selected for record or playback or it can be dedicated to multi-unit operation. In the multi-unit mode, up to a theoretical maximum of 255 dual channel AntiLogPro OEM units can be combined together and controlled as one large multi-unit data logger, all controlled via a single serial port interface.


APPLICATIONS

- Recording important civil or military GPS/GNSS receiver trials data on location.
- Logging output from equipment in ASCII, binary or any other format.
- Monitoring traffic in both directions on an existing RS232 link.
- Recording two equipment outputs which need a common time stamp reference.
- Recording data from equipment that needs to be polled for readings.
- Completely unattended data logging in remote locations.
- Trials where important events need to be logged using operator button pushes.
- Applications that require data to be collected by non-technical staff.
- Ideal for applications that do not have a local source of power for logging.
- Recording from a large number of data sources (AntiLogPro OEM multi-unit).

FLEXIBILITY

AntiLog can record ALL RS232 data transmitted by your RS232 data sources. It does not suffer from data resolution problems experienced by some other RS232 data logging solutions. You can also pre-select, sub sample, filter and time tag incoming data streams independently on up to two recording channels.

You can even transmit user defined commands to your equipment during record either by pressing the front panel buttons or have AntiLog automatically send commands at user defined rates (ideal for taking measurements from equipment which requires data polling).



The built in Real Time Clock allows time tagging of logged data. A Military option ('M') is available to add recording of Military/Government GPS receivers (e.g. ICD-GPS-153).

CONFIGURATION

You configure AntiLog for your needs using a serial port terminal program (e.g. Microsoft HyperTerminal or the free Anticyclone Systems Ltd AntiTermPro application). Use the intuitive menu system you see on the terminal screen in the playback mode to set your options. All settings are non-volatile so they won't be lost when power is removed.

The bootloader (standard on all units) allows the embedded software to be upgraded very simply to the latest release from plain text files which can be supplied over the Internet.

ANTILOG V7.0 STANDARD FEATURE SUMMARY

All OEM and boxed AntiLog products are supplied with the following features as standard:-

General Features

- Cost effective, complete data logging solution.
- Single or independent dual port RS232 data logging available in one unit.
- Two serial ports available from front panel 9 way D connector with adapter cable.
- Fully unattended operation possible including automatic power and log file shut down.
- Up to 1TByte (1024GByte) of non volatile storage options supported.
- At least 60 hours of recording time possible from a single PP3 Alkaline battery
- Extended operation possible with long life PP3 Alkaline cells.
- Dynamic battery health check via menu system with terminal load voltage report.
- Dynamic power management saves power when using slower baud rates.
- Can operate from an external DC power source in the range 4.5 to 18V.
- File system supports real time date and time tagging of session and event information.
- Ability to log the unit supply voltage against time (for power supply monitoring).
- Media recovery feature for comprehensive data recovery.
- OEM product allows access to CMOS 3V3 RS232 levels (selected ports only).
- Built in system 'bootloader' to allow embedded software upgrades via any serial port.

Recording Features (using original AntiLog hardware)

- Records ASCII, binary or any other data combination as standard.
- Can log 230,400 baud data at full rate (no handshaking required) with suitable media.
- Full rate data capture possible from two 115,200 baud data sources at the same time.
- Selected GPS/GNSS NMEA sentences can be logged using NMEA sentence filtering.
- Intelligent data frame sub-sampling for ASCII line formatted data sources (e.g. NMEA).
- ASCII line data can be time tagged with millisecond resolution.
- Binary data can be time tagged using 'N' byte time tagging mode.
- User equipment commands can be sent at user defined rates (equipment polling).
- Can log 'user events' during data logging using the 'On' and 'Off' buttons.
- Can log the logical state and transitions of selected digital input lines during record.
- Independent equipment polling and button event logging for both recording channels

Playback Features (using original AntiLog hardware)

- Full rate RAW playback available.
- 'Real time' playback (including dual serial port) to simulate original equipment output.
- Time shift to simulate live data (e.g. live time and date replacement in NMEA data).
- Playback can be synchronised to external event input (wait on hardware pulse).
- Hexadecimal playback mode to display recorded data as an ASCII hexadecimal dump.
- Hexadecimal playback mode can show recorded time stamps before each data block.

----- *Anticyclone Systems Limited* -----

Registered in England and Wales · Registration number 3597092 · VAT registration number 709 1722 41
Registered office at Brook House, Mint Street, Godalming, Surrey. GU7 1HE

ASL/16/PDS/7.0

- Session headers and time stamp date and time can be embedded in output stream.
- ASLTX2 Data Transfer protocol built in for uploading recorded data to a host machine.

Configuration Features (using original AntiLog hardware)

- Independently programmable transmit and receive baud rates from 110 to 460,800.
- User selectable parity, data bits per character (5 to 8) and stop bits.
- Independent non standard baud rate support per channel (e.g. 11,111 baud).
- Complete sets of user options can be saved with a name and recalled for later use.
- Up to four user equipment commands can be stored for output during record mode.
- Time transfer function to accurately transfer time and date to another AntiLog unit.

ANTILOGPRO ADVANCED FEATURES SUMMARY

The following features are available when running V7.0 on AntiLogPro hardware:-

- High speed operation. Log full rate data at up to 921,600 baud.
- Able to log two 460,800 baud channels at full rate at the same time.
- Selectable ring buffer data storage method to retain only the most recent data.
- Support for a third serial port (auxiliary port) on OEM variant.
- All RS232 input lines individually invertible to log logic as well as RS232 line signals.
- 9 digital states can be logged including two on 9-way D connector protected to $\pm 40V$.
- Settings can easily be transferred from one unit to another via a NULL modem cable.
- 1 pulse per second output available on OEM variant for precise timing applications.
- Support for dual channel GNSS Receiver simulated output option (Option 'G')
- Auxiliary port can be configured for Multi-unit operation (OEM only).
- Status reported by two bi-colour status LEDs

TAILOR MADE OPTIONS

AntiLog V7.0 provides an extremely comprehensive set of features as standard but additional 'Option Packs' available from your AntiLog supplier extend the capabilities still further. Hardware options are generally only available from your AntiLog supplier but software options can be installed after purchase using the built in bootloader application.



Hardware Option 'P': Forced Power (OEM only)

- Starts recording data as soon as power is applied.
- Power may be removed and reapplied at any time to append more data in sessions.
- Suitable for power sources in the range 9.5V to 18V.
- Can power up straight into playback mode rather than record mode if required.
- Can power up in playback based on the state of an "EventIn" digital input (OEM only).
- 'On' and 'Off' buttons still function to record events and transmit equipment commands.
- Ideal for deeply embedded systems where user interaction is not possible or desired.
- The recommend option for OEM multi-unit configurations.

Hardware Option 'G': GNSS Simulated Receiver Output (AntiLogPro only)

- Available as a factory fitted hardware option for AntiLogPro boxed or OEM units only.
- Simulate real time selectable GNSS NMEA output for a user supplied static location.
- Supports NMEA sentences from GPS, GLONASS, Galileo, BeiDou and integrated sources.
- Time stamps in sync with internal time stamping system (and 1PPS output - OEM only).
- Dual channel simulation selectable, each channel with it's own independent settings.
- You can still log two channels of data at the same time including full time stamping.

Software Option 'M': Government and Military GPS receiver logging

- Includes all standard features available in AntiLog.
- ICD-GPS-150, ICD-GPS-153 (ICD-GPS-15x) data stream compatible.
- Two sources of ICD-GPS-15x data can be recorded at once with independent settings.
- LED flashes show when checksum validated message headers are being recorded.
- Time tagging of all IP messages available to millisecond resolution.
- Message 'autoconnect' feature to automatically request user selected message IDs.
- Automatically sends out acknowledgements in response to acknowledge requests.
- Button events, supply voltage and digital input lines can be inserted as IP messages.
- Compatible with RS232 output from SPGR, PLGR, DAGR and similar GPS receivers.
- Selectable 'Real time' playback of ICD-GPS-15x data which uses time tagged data.

Software Option 'D': Force Dual Port Operation

- Forces dual port operation when factory defaults are applied instead of single port.

Software Option 'L': Menu Baud Rate Lock

- Prevents a baud rate reset using the 'On' button at start up if settings lock is active.

Software Option 'X': Extended 'On' button Playback delay

- 'On' button delay required to activate playback mode extended from 1.75 to 5 seconds.
- Reduces chance of inexperienced users accidentally starting AntiLog in playback mode.

Software Option 'N': Nolog

- Unit works in record mode without media present (no data recording desired).
- Can be used to configure equipment with user commands in record mode.
- Ideal for use with 'M' option for configuring ICD-GPS-153 GPS receiver block output.

Software Option 'S': Security

- Adds user password protection for controlled access to the terminal menu system.
- Prevents unauthorised unit configuration inspection or change.



**DON'T RISK LOSING YOUR IMPORTANT
SERIAL PORT DATA!**

For more information please visit www.anticyclone.co.uk or email info@anticyclone.co.uk

Detail may be subject to change without notice. Data applicable to AntiLog boxed and OEM products with embedded software release 7.0

----- *Anticyclone Systems Limited* -----

Registered in England and Wales · Registration number 3597092 · VAT registration number 709 1722 41
Registered office at Brook House, Mint Street, Godalming, Surrey. GU7 1HE

ASL/16/PDS/7.0